

Tumble dryer



Dryer featuring exceptional savings and effortless use



Priority on people

Certified ergonomic design with a human-centered approach for an outstanding user experience

- · Lint filter
 - The horizontal filter drawer is positioned for easy access and cleaning without the need to bend down $\,$
- · Large door opening for easy loading and unloading
- · Easy access to vital parts from front and rear for simple servicing



Long-term savings

Innovative features to save money and time, and embrace a sustainable lifestyle with excellent water evaporation efficiency per kWh

Moisture Balance (optional)
 Helps to stop the drying process at the right time to save on energy costs



Pure control

Monitor your equipment and performance from anywhere, allowing to take action and to improve your business with OnE Laundry - the personal assistant for hygiene validation management, process management and revenue management (optional)




Outstanding productivity

Dry more laundry in less time: a game-changing improvement

· Reversing drum

Minimizes wrinkles and drying time to get an effective and even drying performance with 2 full loads per hour



Global Advanced Hygiene program package* with proven log 6 reduction** disinfection of textiles through the laundry process, fulfilling the criteria of all local approved standards



- · Connection to booking-/payment-system or coin meter
- Stainless steel drum, Stainless steel front
- Fresh air intake
- Exhaust on top (Top evacuation is not available on steam heated tumble dryers)
- Insert for drying special equipment



Images shown are a representation of the product only and

- * Programs available in the standard library of all products, excluding products for specific segments where water temperature is not controllable.
- ** Log 6 reduction equals to 99,9999% viral infectivity reduction. The efficacy of reduction of SARS-CoV-2 and other pathogens in the process is confirmed by RISE (The Research Institute of Sweden) on the basis of Electrolux Professional laboratory data.


Main specifications			TD	5-37	
Rated capacity, filling factor 1:18	kg/lb	37.5/82.7			
filling factor 1:22	kg/lb		30.6	/67.5	
Drum volume	litre	675			
Drum diameter	mm	913			
Heating alternatives					
electric	kW	32.0/40.0			
gas	BTU/h (kW)	14 3400 (42)			
steam at 600-700 kPa	kW	46			
Consumption data*		32.0 kW	40.0 kW	Gas	Steam
Total time at 30.6 kg	min	28	23	23	22
Energy consumption at 30.6 kg	kWh	15.10	15.08	16.42	19.27
Evaporation	g/min	544	676	653	700
Energy kWh/litre water evaporated	kWh/l	0.98	0.98	1.07	1.26
* At rated capacity 100% cotton load at 50% initial moisture dr	yed to 0%.				


Electrical connections								
Heating alternative	Main voltage	Hz	Heating power kW	Total power kW	Recommended fuse A			
Electric heated	220-240V 3 ~ 380-415V 3N/3 ~ 440V 3 ~ 480V 3 ~	50/60 50/60 60	32.0/40.0 32.0/40.0 32.0/40.0 32.0/40.0	33.5/41.5 33.5/41.5 33.5/41.5 33.5/41.5	100/125 50/63 50/63 50/63			
Gas heated / Steam heated	220-240V 1/1N ~ 220-480V 3/3N ~		- -	1.8 1.5	10 10			


Steam, gas and	air connections	TD6-37		
	tion NG/PG Natural gas	ISO 7/1-R kPa kg/h ISO 7/1-R ISO 7/1-R Pa mbar	1" 100-1000 65 1" 1/2" 2000 20	
Air outlet Maximum air flo		Pa mbar ø mm	2800-3700 28-37 200	
Maximum static		m³/h m³/h	1140 / 1140 1140 / 1140 1380 / 1380	
	Electric 50 Hz / 60 Hz Gas 50 Hz / 60 Hz Steam 50 Hz / 60 Hz	Pa Pa Pa	270 / 800 410 / 800 900 / 1100	
Sound levels				
Sound power/pr	essure level at drying*	dB(A)	74/57	
Heat emission				
% of installed po	wer, max	15		
Shipping data**				
Shipping volume	•	net, kg crated, m³	283 3.25	
Dimensions in m	nm			
A Width B(a) Depth B(b) Depth C Height D E F G H I J K L M N			960 1560 1640 1855 660 720 170 1490 200 180 1560 50 480 580 805	

- Control panel
- Door opening ø 810 mm
- 2 3 4 5 6 7 8 Electrical connection
- Gas connection
- Exhaust connection
- Condensate connection
- Steam connection Lint screen
- Sound power levels measured according to ISO 60704.
- Average data. Crated weight/shipping volume depends on configuration. Please contact logistics for exact measures.









Rear side